



75162099



**IP20**

**B.IQ push-button 2gang, KNX - B.IQ, p. white, matt, plastic**

**Technical characteristics**

**Functions**

With room temperature controller	No
Function	for switch, push-button, dimmer and shutter functions

**Compatibility**

Extension unit	extension unit for light scene push-button
----------------	--

**Controls and indicators**

With LED indication	Yes
Number of buttons	2

**Dimensions**

Depth	16.65 mm
Height	88.5 mm
Width	88.5 mm

**Measurement**

Value transmitter	dimming / position value transmitter 1 byte
-------------------	---

**Screen**

With display	No
--------------	----

**Materials**

Colour of labelling	105,105,105
Colour of design line	polar white
RAL colour	RAL 9010 - Pure white
Surface appearance	matt
Type of surface treatment	untreated
Material family	Plastic

**LED control**

LED	with blue operation LED and 4 white status LEDs (labelling field illumination)
-----	--

**Connection**

Bus coupling unit	for bus coupling unit flush-mounted
-------------------	-------------------------------------

**Scope of delivery**

Bus connection included	No
-------------------------	----

**Accessories included**

Box	for installation in single standard wall boxes
Matching products	for additional products to complement the installation in matching colours/materials, refer to the Design platform S.1/B.x ; for plastic frames in the same "style" for additional applications, see the Design line B.7

### Equipment

Number of actuation points	4
With anti-theft/dismantling protection	Yes
Type of configuration	Laserdruck
Product type:	product type: B.IQ

### Safety

REACH conform	Yes
RoHS conform	Yes
Protection	with dismantling protection

### Use conditions

Operating temperature	-5...45 °C
-----------------------	------------

### Identification

Application, usage	KNX - operating systems
Product family	product family: push-button
Main design line	KNX - Berker B.IQ
Secondary design line(s)	KNX ; Berker B.IQ