



75163090

IP20

## B.IQ push-button 3gang, KNX - B.IQ, glass p. white

### Technical characteristics

#### Architecture

Fixing mode flush-mounting

#### Functions

With room temperature controller No

Function for switch, push-button, dimmer and shutter functions

#### Compatibility

Extension unit extension unit for light scene push-button

#### Controls and indicators

With LED indication Yes

Number of buttons 3

#### Dimensions

Assembling height 16.7 mm

Height 88.5 mm

Width 88.5 mm

#### Measurement

Value transmitter dimming / position value transmitter 1 byte

#### Screen

With display No

#### Materials

Colour of design line glass polar white

Colour polarwhite

RAL colour RAL 9010 - Pure white

Material glass

Type of surface treatment Painted

Material family Glass

#### LED control

LED with blue operation LED and 6 white status LEDs (labelling field illumination)

#### Connection

Bus coupling unit for bus coupling unit flush-mounted

#### Scope of delivery

Bus connection included

No

---

### Accessories included

---

Box for installation in single standard wall boxes

Matching products

for glass frames in the same "style" for additional applications, see the Design line B.7, for additional products to complement the installation in matching colours/materials, refer to the Design platform S.1/B.x

---

### Equipment

---

Number of actuation points 6

---

With anti-theft/dismantling protection Yes

---

Product type: product type: B.IQ

---

### Safety

---

Protection index IP IP20

---

Protection with dismantling protection

---

### Use conditions

---

Operating temperature -5...45 °C

---

### Identification

---

Application, usage KNX - operating systems

---

Product family product family: push-button

---

Main design line KNX - Berker B.IQ

---

Secondary design line(s) Berker B.IQ, KNX