



75163594

IP20

B.IQ push-button 3gang comf, KNX - B.IQ, al., al. anodised

Technical characteristics

Architecture

Fixing mode	flush-mounting
-------------	----------------

Functions

With room temperature controller	No
----------------------------------	----

Function	for switch, push-button, dimmer and shutter functions
----------	---

Compatibility

Extension unit	extension unit for light scene push-button
----------------	--

Controls and indicators

With LED indication	Yes
---------------------	-----

Number of buttons	3
-------------------	---

Operation	activation of second user level via object, one push-button operation for switching, pushing, shutters and dimming
-----------	--

Dimensions

Assembling height	16.7 mm
-------------------	---------

Height	88.5 mm
--------	---------

Width	88.5 mm
-------	---------

Measurement

Value transmitter	value transmitter for dimming, position, brightness and temperature values 1 and 2 byte
-------------------	---

Screen

With display	No
--------------	----

Materials

Colour of design line	Aluminium
-----------------------	-----------

Colour	aluminium
--------	-----------

RAL colour	RAL 9006 - White aluminium
------------	----------------------------

Material / workmanship	aluminium, anodised
------------------------	---------------------

Material	Aluminium
----------	-----------

Surface appearance	matt
--------------------	------

Type of surface treatment	Anodised
---------------------------	----------

LED control

LED	with blue operation LED and 6 white status LEDs (labelling field illumination)
-----	--

Connection	
Bus coupling unit	for bus coupling unit flush-mounted
Settings	
Supported configuration modes	system, PB
Parameterisation	single and two push-button operation parameterisable
Scope of delivery	
Bus connection included	No
Accessories included	
Box	for installation in single standard wall boxes
Matching products	for additional products to complement the installation in matching colours/materials, refer to the Design platform S.1/B.x, for aluminium frames in the same "style" for additional applications, see the Design line B.7
Equipment	
Number of actuation points	6
With anti-theft/dismantling protection	Yes
Product type:	product type: B.IQ
Safety	
Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes
Protection	with dismantling protection
Alarm	alarm telegram after disconnection from bus coupling unit 1 bit or 1 byte
Use conditions	
Operating temperature	-5...45 °C
Identification	
Application, usage	KNX - operating systems
Product family	product family: push-button
Main design line	KNX - Berker B.IQ
Secondary design line(s)	KNX, Berker B.IQ