



75164099

IP20

B.IQ push-button 4gang, KNX - B.IQ, p. white, matt, plastic

Technical characteristics

Architecture

Fixing mode flush-mounting

Functions

With room temperature controller No

Function for switch, push-button, dimmer and shutter functions

Compatibility

Extension unit extension unit for light scene push-button

Controls and indicators

With LED indication Yes

Number of buttons 4

Dimensions

Height 118.1 mm

Width 88.5 mm

Measurement

Value transmitter dimming / position value transmitter 1 byte

Screen

With display No

Materials

Colour of design line polar white

Colour polarwhite

RAL colour RAL 9010 - Pure white

Material thermoplastic

Surface appearance matt

Type of surface treatment untreated

Material family Plastic

LED control

LED with blue operation LED and 8 white status LEDs

Connection

Bus coupling unit for bus coupling unit flush-mounted

Scope of delivery

Bus connection included No

Accessories included

Box	for installation in single standard wall boxes
Matching products	for plastic frames in the same "style" for additional applications, see the Design line B.7, for additional products to complement the installation in matching colours/materials, refer to the Design platform S.1/B.x

Equipment

Number of actuation points	8
With anti-theft/dismantling protection	Yes
Type of configuration	Laserdruck
Product type:	product type: B.IQ

Safety

Protection index IP	IP20
Protection	with dismantling protection

Use conditions

Operating temperature	-5...45 °C
-----------------------	------------

Identification

Application, usage	KNX - operating systems
Product family	product family: push-button
Main design line	KNX - Berker B.IQ
Secondary design line(s)	KNX, Berker B.IQ