




75164373

IP20



## Technical characteristics

### Architecture

Fixing mode flush-mounting

### Functions

With room temperature controller No

Function for switch, dimmer and shutter functions

### Compatibility

Extension unit extension unit for light scene push-button

### Controls and indicators

With LED indication Yes

Number of buttons 4

### Dimensions

Labelling field length (W x H) 66.8 x 25 mm

Height 111.3 mm

Width 70.5 mm

### Measurement

Value transmitter dimming / position value transmitter 1 byte

### Screen

With display No

### Materials

Colour of design line stainless steel

Colour stainless steel

RAL colour RAL 9022 - Pearl light grey

Material Plastic/metal

Material for printing Paper

Surface appearance matt

Type of surface treatment Painted

Material family Plastic

### LED control

LED - KNX with white operation LED and 8 red status LEDs

### Connection

Bus coupling unit for bus coupling unit flush-mounted

### Scope of delivery

**Accessories included**

Box	for installation in single standard wall boxes
-----	--

**Equipment**

Number of actuation points	8
With anti-theft/dismantling protection	Yes
Type of configuration	Beschriftungsfeld(er) - Folie
Product type:	product type: push-button 4gang

**Use cases**

Frame	only for frame with large cut-out
-------	-----------------------------------

**Use**

Differentiation characteristic 1 - Sales	with labelling fields
Differentiation characteristic 3 - Sales	with horizontal operation

**Safety**

Protection index IP	IP20
Protection	with dismantling protection

**Use conditions**

Operating temperature	-5...45 °C
-----------------------	------------

**Identification**

Application, usage	KNX - operating systems
Product family	product family: push-button
Secondary design line(s)	KNX, Berker K.5

**Instructions**

Special note text	Use only in combination with frame frame with large cut-out.
-------------------	--