



85141139

**Button 1gang, R.1/R.3/1930/R.cl., p. white glossy**

**Technical characteristics**

**Controls and indicators**

Operation with 2-push-buttons operation concept

**Main electrical features**

Nominal voltage 12 V

**Voltage**

Operating voltage via insert

**Dimensions**

Diameter 57.4 mm

**Materials**

Colour of design line polar white

Colour polarwhite

Material thermoplastic

Material for printing ASA polar white

**Settings**

Shading parameter R1\_biały

Laser parameter R1\_weiß

**Equipment**

Type of configuration Laserdruck

**Use conditions**

Operating temperature -5...45 °C

Relative humidity (without condensation) 0...65 % (without condensation)

**Identification**

Application, usage Light control

Main design line Berker R.1/R.3/R.8/Serie 1930/R.classic

Secondary design line(s) Berker R.1, Berker R.3, Berker R.8

**Instructions**

Special note text

Note: When integrating this product into the Serie 1930, the 1gang frame for centre plate Ø 58 mm, order no.: 1382 0... may only be used. Installation in multiple combinations of the Serie 1930 is not possible!