



85142126

**Button 2gang, Q.x, ant. velvety, lacq.**

**Technical characteristics**

**Controls and indicators**

Operation with 2-push-buttons operation concept per series

**Main electrical features**

Nominal voltage 12 V

**Voltage**

Operating voltage via insert

**Materials**

Colour of design line anthracite

Material / workmanship lacquered

**Equipment**

Brightness switch-on brightness level for use on dimmer insert, power failure proof, storable

**Safety**

Halogen free No

Protection with dismantling protection

**Use conditions**

Operating temperature -5...45 °C

Energy-saving low intrinsic energy requirement

Relative humidity (without condensation) 0...65 % (without condensation)

**Identification**

Application, usage Light control

Main design line Berker Q.1/Q.3/Q.7/Q.9

Secondary design line(s) Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9