



85142129

## Button 2gang, Q.x, p. white velvety

### Technical characteristics

#### Controls and indicators

Operation with 2-push-buttons operation concept per series

#### Main electrical features

Nominal voltage 12 V

#### Voltage

Operating voltage via insert

#### Materials

Colour of design line polar white

#### Equipment

Brightness switch-on brightness level for use on dimmer insert, power failure proof, storable

#### Safety

Halogen free No

Protection with dismantling protection

#### Use conditions

Operating temperature -5...45 °C

Energy-saving low intrinsic energy requirement

Relative humidity (without condensation) 0...65 % (without condensation)

#### Identification

Application, usage Light control

Main design line Berker Q.1/Q.3/Q.7/Q.9

Secondary design line(s) Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9