



85241131

## Shutter push-button, R.1/R.3/1930/R.cl., black glossy

### Technical characteristics

#### Functions

|                              |           |
|------------------------------|-----------|
| Venetian blind movement time | 2 mn      |
| Running time                 | max. 2 mn |

#### Main electrical features

|                 |      |
|-----------------|------|
| Nominal voltage | 12 V |
| Frequency       | - Hz |

#### Dimensions

|          |         |
|----------|---------|
| Diameter | 57.6 mm |
|----------|---------|

#### Materials

|                       |               |
|-----------------------|---------------|
| Colour of design line | black         |
| Colour                | black         |
| Material              | thermoplastic |

#### Installation, mounting

|                   |                 |
|-------------------|-----------------|
| Installation mode | clamp fastening |
|-------------------|-----------------|

#### Settings

|                                    |                            |
|------------------------------------|----------------------------|
| Lamella adjusting time             | (adjustable) 50 ms...2.5 s |
| Minimum slat adjustment time       | ≈ 250 ms                   |
| Delay time, adjustable             | 0...500 s                  |
| Lamella adjustment on button-press | < 0.4 s                    |

#### Equipment

|  |         |
|--|---------|
| Self-retaining for 2 min on button-press | > 0.4 s |
| Change-over time for change of direction | < 0.6 s |

#### Safety

|            |                             |
|------------|-----------------------------|
| Protection | with dismantling protection |
|------------|-----------------------------|

#### Use conditions

|  |                                 |
|--|---------------------------------|
| Operating temperature                    | -5...45 °C                      |
| Relative humidity (without condensation) | 0...65 % (without condensation) |

#### Identification

|                          |   |
|--------------------------|---|
| Application, usage       | Blind control                           |
| Main design line         | Berker R.1/R.3/R.8/Serie 1930/R.classic |
| Secondary design line(s) | Berker R.1, Berker R.3, Berker R.8      |

## Instructions

---

Can be switched to orientation led by extension unit.  
; Note: When integrating this product into the Serie 1930, the 1gang frame for centre plate Ø 58 mm, order no.: 1382 0... may only be used. Installation in multiple combinations of the Serie 1930 is not possible!

Special note text