



85241131

## Shutter push-button, R.1/R.3/1930/R.cl., black glossy

### Technical characteristics

#### Functions

Venetian blind movement time	2 mn
Running time	max. 2 mn

Function	Memory function for automatic execution of learned up and down times with position ; Party function, no execution of automatic, radio and extension unit commands (lock-out protection)
----------	-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

#### Controls and indicators

Operation	activation of the party function using buttons in up and down direction > 20 sec.
-----------	-----------------------------------------------------------------------------------

#### Main electrical features

Nominal voltage	12 V
Frequency	- Hz

#### Dimensions

Diameter	57.6 mm
----------	---------

#### Materials

Colour of design line	black
Colour	black

#### LED control

LED	LED application module/insert compatibility display ; with status LED for memory and party function, red/orange ; with indicator LED for lock-out protection
-----	--------------------------------------------------------------------------------------------------------------------------------------------------------------

#### Installation, mounting

Installation mode	clamp fastening
-------------------	-----------------

#### Settings

Lamella adjusting time	(adjustable) 50 ms...2.5 s
Minimum slat adjustment time	≈ 250 ms
Delay time, adjustable	0...500 s
Lamella adjustment on button-press	< 0.4 s

#### Equipment

Self-retaining for 2 min on button-press	> 0.4 s
Change-over time for change of direction	< 0.6 s

#### Safety

Halogen free	No
--------------	----

Protection

with dismantling protection

---

**Use conditions**

Operating temperature

-5...45 °C

Energy-saving

low intrinsic energy requirement

Relative humidity (without condensation)

0...65 % (without condensation)

---

**Identification**

Application, usage

Blind control

Main design line

Berker R.1/R.3/R.8/Serie 1930/R.classic

Secondary design line(s)

Electronics platform ; Berker R.1 ; Berker R.3 ;  
Berker R.8

---

**Instructions**

Special note text

Can be switched to orientation led by extension unit.  
; Note: When integrating this product into the Serie  
1930, the 1gang frame for centre plate Ø 58 mm,  
order no.: 1382 0... may only be used. Installation in  
multiple combinations of the Serie 1930 is not  
possible!