



91933

**Contact protection box 3gang, Integro module inserts, grey**

**Technical characteristics**

**Dimensions**

Insertion depth	38 mm
Length	168 mm
Width	168 mm

**Materials**

Colour of design line	grey
Colour independent of design lines	Grey

**Installation, mounting**

Opening	5 knock out openings
Installation mode	for vertical and horizontal mounting
Fixing of devices	screwing

**Cable**

Cable Ø	max. 10 mm
Wire	with 6 cable entries, 1 per side, top, bottom and 2 rear

**Safety**

REACH conform	No
RoHS conform	Yes
Flame resistant	according to VDE 0606-1

**Identification**

Main design line	Berker Integro module inserts
Secondary design line(s)	Berker Integro ; Berker Integro Module inserts ; ACCESSORIES ; Berker Integro Flow ; Berker Integro Pure ; Berker Integro Classic

**Instructions**

Special note text	Restricted installation options apply if the strain relief is mounted on the front face. All devices can optionally be arranged vertically or horizontally. Only suitable for 3gang frames!
Information text	Strain relief not suitable for flat cables.