



936552509

Series switch, common input terminal, Integro - Design Flow/Pure, pol wh gl

Technical characteristics

Architecture

Type of control unit double rocker

Configuration

Switch mode series

Antibacterial treatment No

Compatibility

IFTTT support available No

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Electric current

Switching current 10 AX (100 W Self Ballasted Lamp (SBL))

Dimensions

Depth 25 mm

Height 55.5 mm

Width 55.5 mm

Materials

Colour white

RAL colour RAL 9010 - Pure white

Material thermoplastic

Connection

Type of connection with screw terminals

Type of connection Screw connection

Equipment

Lighting without lighting (cannot be illuminated)

Heating switch No

Use cases

Application Light control

Safety

Protection index IP IP20

REACH conform Yes

Identification

| | |
|--------------------------|--|
| Appliance switch type | No |
| Secondary design line(s) | Berker Integro Flow, Berker Integro Pure |