



936552509

**Series switch, common input terminal, Integro - Design Flow/Pure, pol wh gl**

**Technical characteristics**

**Architecture**

Type of control unit	double rocker
Number of keys	2

**Configuration**

Switch mode	series
Antibacterial treatment	No

**Compatibility**

IFTTT support available	No
-------------------------	----

**Main electrical features**

Nominal voltage	250 V
Rated voltage	250 V AC

**Electric current**

Switching current	10 AX (100 W Self Ballasted Lamp (SBL))
-------------------	---

**Dimensions**

Depth	25 mm
Height	55.5 mm
Width	55.5 mm

**Materials**

Colour	white
RAL colour	RAL 9010 - Pure white
Surface appearance	glossy

**Connection**

Type of connection	with screw terminals
--------------------	----------------------

**Equipment**

Lighting	without lighting (cannot be illuminated)
Heating switch	No

**Use cases**

Application	Light control
-------------	---------------

**Safety**

REACH conform	Yes
RoHS conform	Yes

**Identification**

---

Appliance switch type	No
Main design line	Berker Integro Flow/Pure
Secondary design line(s)	Berker Integro Flow ; Berker Integro Pure

---