



936552509

Series switch, common input terminal, Integro - Design Flow/Pure, pol wh gl

Technical characteristics

Architecture

Type of control unit	double rocker
Number of keys	2

Configuration

Switch mode	series
Antibacterial treatment	No

Compatibility

IFTTT support available	No
-------------------------	----

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC

Electric current

Switching current	10 AX (100 W Self Ballasted Lamp (SBL))
-------------------	---

Dimensions

Depth	25 mm
Height	55.5 mm
Width	55.5 mm

Materials

Colour	white
RAL colour	RAL 9010 - Pure white
Surface appearance	glossy

Connection

Type of connection	with screw terminals
Type of connection	Screw connection

Equipment

Lighting	without lighting (cannot be illuminated)
Heating switch	No

Use cases

Application	Light control
-------------	---------------

Safety

REACH conform	Yes
---------------	-----

RoHS conform

Yes

Identification

Appliance switch type

No

Main design line

Berker Integro Flow/Pure

Secondary design line(s)

Berker Integro Flow ; Berker Integro Pure