



936552524

Series switch, com input term, Integro - Design Flow/Pure, stain steel m, lacq

## Technical characteristics

### Architecture

Type of control unit double rocker

### Configuration

Switch mode series

Antibacterial treatment No

### Compatibility

IFTTT support available No

### Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

### Electric current

Switching current 10 AX (100 W Self Ballasted Lamp (SBL))

### Dimensions

Depth 25 mm

Height 55.5 mm

Width 55.5 mm

### Materials

Colour stainless steel optics

RAL colour RAL 9022 - Pearl light grey

Material thermoplastic

Surface appearance matt

### Installation, mounting

Installation mode for screw fastening

### Connection

Type of connection with screw terminals

Type of connection Screw connection

### Equipment

Lighting without lighting (cannot be illuminated)

Heating switch No

### Use cases

Application Light control

**Safety**

Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes

**Identification**

Appliance switch type	No
Secondary design line(s)	Berker Integro Flow, Berker Integro Pure