



936552524

Series switch, com input term, Integro - Design Flow/Pure, stain steel m, lacq

Technical characteristics

Architecture

Type of control unit	double rocker
Number of keys	2
Fixing mode	Built-in installation

Configuration

Switch mode	series
Antibacterial treatment	No

Compatibility

IFTTT support available	No
-------------------------	----

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC

Electric current

Switching current	10 AX (100 W Self Ballasted Lamp (SBL))
-------------------	---

Dimensions

Depth	25 mm
Height	55.5 mm
Width	55.5 mm

Materials

Colour	stainless steel optics
RAL colour	RAL 9022 - Pearl light grey
Material	thermoplastic
Surface appearance	matt

Installation, mounting

Installation mode	for screw fastening
-------------------	---------------------

Connection

Type of connection	with screw terminals
Type of connection	Screw connection

Equipment

Lighting	without lighting (cannot be illuminated)
Heating switch	No

Use cases

Application	Light control
-------------	---------------

Safety

Protection index IP	IP20
---------------------	------

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Identification

Appliance switch type	No
-----------------------	----

Main design line	Berker Integro Flow/Pure
------------------	--------------------------

Secondary design line(s)	Berker Integro Flow, Berker Integro Pure
--------------------------	--