



936562505

## Change-over switch, Integro - Design Flow/Pure, anthracite matt

### Technical characteristics

#### Architecture

Type of control unit	single rocker
Number of keys	1

#### Configuration

Switch mode	Off/change-over
Antibacterial treatment	No

#### Compatibility

IFTTT support available	No
-------------------------	----

#### Controls and indicators

Push-buttons	No
--------------	----

#### Main electrical features

Nominal voltage	250 V
-----------------	-------

#### Electric current

Switching current	10 AX (100 W Self Ballasted Lamp (SBL))
-------------------	---

#### Dimensions

Depth	25 mm
Height	55.5 mm
Width	55.5 mm

#### Materials

Surface appearance	matt
--------------------	------

#### Installation, mounting

Installation mode	for screw fastening
-------------------	---------------------

#### Connection

Type of connection	with screw terminals
--------------------	----------------------

#### Equipment

Lighting	without lighting (cannot be illuminated)
Heating switch	No

#### Use cases

Application	Light control
-------------	---------------

#### Safety

Protection index IP	IP44
REACH conform	Yes
RoHS conform	Yes
<b>Identification</b>	
Appliance switch type	No
Main design line	Berker Integro Flow/Pure
Secondary design line(s)	Berker Integro Flow ; Berker Integro Pure