



936712524

**p-b, NO contact, screw terms, Integro - Design Flow/Pure, stain steel m, lacq**

#### Technical characteristics

##### Architecture

Type of control unit single rocker

##### Compatibility

IFTTT support available No

##### Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

##### Electric current

Momentary-contact current 10 A

##### Dimensions

Depth 25 mm

Height 55.5 mm

Width 55.5 mm

##### Materials

Colour stainless steel optics

RAL colour RAL 9022 - Pearl light grey

Material thermoplastic

Surface appearance matt

##### Connection

Type of connection with screw terminals

##### Use cases

Application Light control

##### Use

Differentiation characteristic 3 - Sales with screw terminals

##### Safety

Protection index IP IP44

##### Identification

Secondary design line(s) Berker Integro Flow, Berker Integro Pure

##### Instructions

Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with sealing (order no. 91853), frame with imprint "IP44" and contact protection box.

Special note text