



9419505

**SCHUKO sock. outl., enh. cont. prot., screw term, Int. mod. inserts, black matt**

**Technical characteristics**

**Architecture**

Design according to DIN 49440

**Configuration**

Number of modules 1

**Main electrical features**

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50 Hz

Rated current 16 A

**Electric current**

Rated current 16 A

**Dimensions**

Installation depth, flush-mounted boxes 32 mm

**Cover, door**

Cover Central cover plate

**Materials**

Colour of design line black

Colour black

Colour black

Material thermoplastic

Surface appearance matt

Metallic colour No

**Installation, mounting**

Installation mode without spreader claws

**Connection**

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with screw terminals

**Use**

Differentiation characteristic 2 - Sales with enhanced touch protection

Differentiation characteristic 3 - Sales Screw terminals

---

**Safety**

|   |                             |
|---|-----------------------------|
| IK protection code against mechanical impacts | 05                          |
| Protection index IP                           | IP44                        |
| Protection                                    | Enhanced contact protection |
| With enhanced contact protection              | Yes                         |

---

**Identification**

|                          |   |
|--------------------------|---|
| Main design line         | Berker Integro module inserts   |
| Secondary design line(s) | Berker Integro Module inserts, Berker Integro Classic, Berker Integro Flow, Berker Integro Pure |

---

**Instructions**

|                   |  |
|-------------------|--|
| Special note text | Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with sealing (order no. 91853), frame with hinged lid (imprint "IP44") and contact protection box. |
|-------------------|--|