



941952506

SCHUKO sock. outl., enh. cont. prot., screw term, Int. module inserts, grey matt

Technical characteristics

Architecture

Design according to DIN 49440

Configuration

Number of modules 1

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50 Hz

Rated current 16 A

Electric current

Rated current 16 A

Dimensions

Installation depth, flush-mounted boxes 32 mm

Cover, door

Cover Central cover plate

Materials

Colour of design line grey

Colour iron grey

Colour grey

Material thermoplastic

Surface appearance matt

Metallic colour No

Installation, mounting

Installation mode without spreader claws

Connection

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with screw terminals

Use

Differentiation characteristic 2 - Sales with enhanced touch protection

Differentiation characteristic 3 - Sales Screw terminals

Safety

IK protection code against mechanical impacts	05
Protection index IP	IP44
Protection	Enhanced contact protection
With enhanced contact protection	Yes

Identification

Main design line	Berker Integro module inserts
Secondary design line(s)	Berker Integro Module inserts, Berker Integro Classic, Berker Integro Flow, Berker Integro Pure

Instructions

Special note text	Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with sealing (order no. 91853), frame with hinged lid (imprint "IP44") and contact protection box.
-------------------	--