



947782501

SCHUKO socket outlet, with plug-in terminals, Integro module inserts, brown matt

Technical characteristics

Architecture

Design according to DIN 49440

Configuration

Number of modules 1

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50 Hz

Rated current 16 A

Electric current

Rated current 16 A

Dimensions

Insertion depth 32.7 mm

Installation depth, flush-mounted boxes 32 mm

Cover, door

Cover Central cover plate

Materials

Colour of design line brown

Surface appearance matt

Material / surface thermoplastic centre plate, matt ; duroplast base

Metallic colour No

Installation, mounting

Installation mode without spreader claws

Connection

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with plug-in terminals

Contact contacts made of copper alloy

Use

Differentiation characteristic 3 - Sales with plug-in terminals

Standards

Safety

IK protection code against mechanical impacts	05
Protection index IP	IP44
REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Protection	without enhanced contact protection

Identification

Main design line	Berker Integro module inserts
Secondary design line(s)	Berker Integro Module inserts ; Berker Integro Classic ; Berker Integro Flow ; Berker Integro Pure

Instructions

Special note text	Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with sealing (order no. 91853), frame with hinged lid (imprint "IP44") and contact protection box.
-------------------	--
