



947782503

SCHUKO socket outlet, with plug-in terminals, Integro module inserts, black matt

Technical characteristics

Architecture

Design according to DIN 49440

Configuration

Number of modules 1

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50 Hz

Rated current 16 A

Electric current

Rated current 16 A

Dimensions

Insertion depth 32.7 mm

Installation depth, flush-mounted boxes 32 mm

Cover, door

Cover Central cover plate

Materials

Colour of design line black

Colour black

Surface appearance matt

Material / surface duroplast base ; thermoplastic centre plate, matt

Metallic colour No

Installation, mounting

Installation mode without spreader claws

Connection

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with plug-in terminals

Contact contacts made of copper alloy

Use

Differentiation characteristic 3 - Sales with plug-in terminals

Standards

Standard	NEN 1010
----------	----------

Safety

IK protection code against mechanical impacts	05
---	----

Protection index IP	IP44
---------------------	------

Halogen free	No
--------------	----

Protection	without enhanced contact protection
------------	-------------------------------------

Identification

Main design line	Berker Integro module inserts
------------------	-------------------------------

Secondary design line(s)	Berker Integro Module inserts ; Berker Integro Classic ; Berker Integro Flow ; Berker Integro Pure
--------------------------	--

Instructions

Special note text	Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with sealing (order no. 91853), frame with hinged lid (imprint "IP44") and contact protection box.
-------------------	--