



947782503

**SCHUKO socket outlet, with plug-in terminals, Integro module inserts, black matt**

**Technical characteristics**

**Architecture**

Design according to DIN 49440

**Configuration**

Number of modules 1

**Main electrical features**

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50 Hz

Rated current 16 A

**Electric current**

Rated current 16 A

**Dimensions**

Insertion depth 32.7 mm

Installation depth, flush-mounted boxes 32 mm

**Cover, door**

Cover Central cover plate

**Materials**

Colour of design line black

Colour black

Colour black

Material thermoplastic

Surface appearance matt

Metallic colour No

**Installation, mounting**

Installation mode without spreader claws

**Connection**

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with plug-in terminals

**Safety**

IK protection code against mechanical impacts 05

Protection index IP	IP44
Protection	without enhanced contact protection
<b>Identification</b>	
Main design line	Berker Integro module inserts
Secondary design line(s)	Berker Integro Module inserts, Berker Integro Classic, Berker Integro Flow, Berker Integro Pure
<b>Instructions</b>	
Special note text	Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with sealing (order no. 91853), frame with hinged lid (imprint "IP44") and contact protection box.