



947782505

**SCHUKO socket outlet, w. plug-in terminals, Int. module inserts, anthracite matt**

**Technical characteristics**

**Architecture**

Design according to DIN 49440

**Configuration**

Number of modules 1

**Main electrical features**

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50 Hz

Rated current 16 A

**Electric current**

Rated current 16 A

**Dimensions**

Insertion depth 32.7 mm

Installation depth, flush-mounted boxes 32 mm

**Cover, door**

Cover Central cover plate

**Materials**

Colour of design line anthracite

Surface appearance matt

Material / surface thermoplastic centre plate, matt ; duroplast base

Metallic colour No

**Installation, mounting**

Installation mode without spreader claws

**Connection**

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with plug-in terminals

Contact contacts made of copper alloy

**Use**

Differentiation characteristic 3 - Sales with plug-in terminals

**Standards**

**Safety**

---

IK protection code against mechanical impacts	05
Protection index IP	IP44
REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Protection	without enhanced contact protection

---

**Identification**

---

Main design line	Berker Integro module inserts
Secondary design line(s)	Berker Integro Module inserts ; Berker Integro Classic ; Berker Integro Flow ; Berker Integro Pure

---

**Instructions**

---

Special note text	Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with sealing (order no. 91853), frame with hinged lid (imprint "IP44") and contact protection box.
-------------------	--

---