



947792506

**SCHUKO sock. outl., enh. cont. prot., plug-in term, Int. mod. inserts, grey matt**

**Technical characteristics**

**Architecture**

Design according to DIN 49440

**Configuration**

Number of modules 1

**Main electrical features**

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50 Hz

Rated current 16 A

**Electric current**

Rated current 16 A

**Dimensions**

Installation depth, flush-mounted boxes 32 mm

**Cover, door**

Cover Central cover plate

**Materials**

Colour of design line grey

Surface appearance matt

Metallic colour No

**Installation, mounting**

Installation mode without spreader claws

**Connection**

Connection terminals according to IEC 60884-1

Connection terminals according to VDE 0620-1

Type of connection with plug-in terminals

**Use**

Differentiation characteristic 2 - Sales with enhanced touch protection

Differentiation characteristic 3 - Sales Plug-in terminals

**Standards**

Standard NEN 1010

**Safety**

IK protection code against mechanical impacts	05
Protection index IP	IP44
REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Protection	Enhanced contact protection
With enhanced contact protection	Yes

#### Identification

Main design line	Berker Integro module inserts
Secondary design line(s)	Berker Integro Module inserts ; Berker Integro Classic ; Berker Integro Flow ; Berker Integro Pure

#### Instructions

Special note text	Only suitable for splash-protected IP44 flush-mounted installation when used in conjunction with sealing (order no. 91853), frame with hinged lid (imprint "IP44") and contact protection box.
-------------------	--