



9626205

Integro Insert-British Standard Socket Outlet with Earth Contact, Black Matt

Technical characteristics

Architecture

Fixing mode	Built-in installation
Number of poles	2pole + earth

Configuration

Number of modules	1
-------------------	---

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50 Hz
Rated current	13 A

Dimensions

Installation depth, flush-mounted boxes	20 mm
---	-------

Cover, door

Cover	Central cover plate
-------	---------------------

Materials

Colour of design line	black
Colour	black
Colour	black
RAL colour	RAL 9011 - Graphite black
Material	thermoplastic
Surface appearance	matt
Metallic colour	No

Installation, mounting

Installation mode	for screw fastening
-------------------	---------------------

Connection

Type of connection	with screw terminals
--------------------	----------------------

Use

Differentiation characteristic 2 - Sales	with enhanced touch protection
Differentiation characteristic 3 - Sales	Screw terminals

Standards

Standard	BS 1363
----------	---------

Safety

IK protection code against mechanical impacts

05

Protection

Enhanced contact protection

Identification

Main design line

Berker Integro module inserts

Secondary design line(s)

Berker Integro Module inserts, Berker Integro Classic, Berker Integro Flow, Berker Integro Pure