



962622502

Integro Inserts-British Standard Socket with Earthing Contact, Polar White Matt

Technical characteristics

Architecture

Number of poles	2pole + earth
-----------------	---------------

Configuration

Number of modules	1
-------------------	---

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50 Hz
Rated current	13 A

Dimensions

Installation depth, flush-mounted boxes	20 mm
---	-------

Cover, door

Cover	Central cover plate
-------	---------------------

Materials

Colour of design line	polar white
Colour	white
RAL colour	RAL 9010 - Pure white
Surface appearance	matt
Metallic colour	No

Installation, mounting

Installation mode	for screw fastening
-------------------	---------------------

Connection

Type of connection	with screw terminals
--------------------	----------------------

Use

Differentiation characteristic 2 - Sales	with enhanced touch protection
Differentiation characteristic 3 - Sales	Screw terminals

Standards

Standard	BS 1363
----------	---------

Safety

IK protection code against mechanical impacts	05
REACH conform	No

RoHS conform	Yes
Halogen free	Yes
Protection	Enhanced contact protection
Identification	
Main design line	Berker Integro module inserts
Secondary design line(s)	Berker Integro Module inserts ; Berker Integro Classic ; Berker Integro Flow ; Berker Integro Pure