



962622506

Integro Inserts-British Standard Socket with Earthing Contact, Grey Matt

Technical characteristics

Architecture

Number of poles 2pole + earth

Configuration

Number of modules 1

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50 Hz

Rated current 13 A

Dimensions

Installation depth, flush-mounted boxes 20 mm

Cover, door

Cover Central cover plate

Materials

Colour of design line grey

Surface appearance matt

Metallic colour No

Installation, mounting

Installation mode for screw fastening

Connection

Type of connection with screw terminals

Use

Differentiation characteristic 2 - Sales with enhanced touch protection

Differentiation characteristic 3 - Sales Screw terminals

Standards

Standard BS 1363

Safety

IK protection code against mechanical impacts 05

REACH conform Yes

RoHS conform Yes

Protection Enhanced contact protection

Identification

Main design line

Berker Integro module inserts

Secondary design line(s)

Berker Integro Module inserts ; Berker Integro Classic ; Berker Integro Flow ; Berker Integro Pure