



962622506

## Integro Inserts-British Standard Socket with Earthing Contact, Grey Matt

### Technical characteristics

#### Architecture

Fixing mode	Built-in installation
Number of poles	2pole + earth

#### Configuration

Number of modules	1
-------------------	---

#### Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50 Hz
Rated current	13 A

#### Dimensions

Installation depth, flush-mounted boxes	20 mm
---	-------

#### Cover, door

Cover	Central cover plate
-------	---------------------

#### Materials

Colour of design line	grey
Colour	iron grey
Colour	grey
RAL colour	RAL 7038 - Agate grey
Material	thermoplastic
Surface appearance	matt
Metallic colour	No

#### Installation, mounting

Installation mode	for screw fastening
-------------------	---------------------

#### Connection

Type of connection	with screw terminals
--------------------	----------------------

#### Use

Differentiation characteristic 2 - Sales	with enhanced touch protection
Differentiation characteristic 3 - Sales	Screw terminals

#### Standards

Standard	BS 1363
----------	---------

<b>Safety</b>	
IK protection code against mechanical impacts	05
REACH conform	Yes
RoHS conform	Yes
Protection	Enhanced contact protection
<b>Identification</b>	
Main design line	Berker Integro module inserts
Secondary design line(s)	Berker Integro Module inserts, Berker Integro Classic, Berker Integro Flow, Berker Integro Pure