



962622506

## Integro Inserts-British Standard Socket with Earthing Contact, Grey Matt

### Technical characteristics

#### Architecture

Number of poles 2pole + earth

#### Configuration

Number of modules 1

#### Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50 Hz

Rated current 13 A

#### Dimensions

Installation depth, flush-mounted boxes 20 mm

#### Cover, door

Cover Central cover plate

#### Materials

Colour of design line grey

Colour iron grey

Colour grey

Material thermoplastic

Surface appearance matt

Metallic colour No

#### Installation, mounting

Installation mode for screw fastening

#### Connection

Type of connection with screw terminals

#### Use

Differentiation characteristic 2 - Sales with enhanced touch protection

Differentiation characteristic 3 - Sales Screw terminals

#### Safety

IK protection code against mechanical impacts 05

Protection Enhanced contact protection

#### Identification

Main design line

Berker Integro module inserts

Secondary design line(s)

Berker Integro Module inserts, Berker Integro Classic, Berker Integro Flow, Berker Integro Pure