



BA7A100030

Slotted panel trunking made of PVC BA7A 100x30mm grey

Technical characteristics

Architecture

Flexible	No
----------	----

Configuration

Side wall configuration	Slotted
-------------------------	---------

Electric current

Current leak stable	Yes
---------------------	-----

Dimensions

Trunking height	100 mm
-----------------	--------

Length	2000 mm
--------	---------

Trunking width	30 mm
----------------	-------

Slot width	6 mm
------------	------

Tongue width	6.5 mm
--------------	--------

Cover, door

Lid shape	loose
-----------	-------

Materials

Colour	stone grey
--------	------------

Material	PVC
----------	-----

Material group	plastic
----------------	---------

Installation, mounting

Base punching	EN 50085-2-3:1999
---------------	-------------------

Cable

Number of wires 1,5 mm ² - 40% filling degree	88
--	----

Internal/useful cross section	2321 mm ²
-------------------------------	----------------------

Number of wires 2,5 mm ² - 40% filling degree	63
--	----

Number of wires 1,0 mm ² - 40% filling degree	122
--	-----

Standards

European directive RoHs	voluntary compliance
-------------------------	----------------------

Safety

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

