



BA7A100040

Slotted panel trunking made of PVC BA7A 100x40mm grey

Technical characteristics

Architecture

Flexible No

Configuration

Side wall configuration Slotted

Electric current

Current leak stable Yes

Dimensions

Trunking height 100 mm

Length 2000 mm

Trunking width 40 mm

Slot width 6 mm

Tongue width 6.5 mm

Cover, door

Lid shape loose

Materials

Colour stone grey

Material PVC

Material group plastic

Installation, mounting

Base punching EN 50085-2-3:1999

Fixing type bottom punching

Cable

Number of wires 1,5 mm² - 40% filling degree 125

Internal/useful cross section 3328 mm²

Number of wires 2,5 mm² - 40% filling degree 89

Number of wires 1,0 mm² - 40% filling degree 173

Standards

Approvals EN50085-2-3

European directive RoHS voluntary compliance