



BA7A25025

## Slotted panel trunking made of PVC BA7A 25x25mm grey

### Technical characteristics

#### Architecture

Flexible No

#### Configuration

Side wall configuration Slotted

#### Electric current

Current leak stable Yes

#### Dimensions

Trunking height 25 mm

Length 2000 mm

Trunking width 25 mm

Slot width 6 mm

Tongue width 6.5 mm

#### Cover, door

Lid shape loose

#### Materials

Colour stone grey

Material group plastic

Type of surface treatment untreated

#### Installation, mounting

Base punching EN 50085-2-3:1999

#### Cable

Number of wires 1,5 mm<sup>2</sup> - 40% filling degree 10

Internal/useful cross section 275 mm<sup>2</sup>

Number of wires 2,5 mm<sup>2</sup> - 40% filling degree 7

Number of wires 1,0 mm<sup>2</sup> - 40% filling degree 14

#### Standards

European directive RoHS voluntary compliance

UL 94 classification V0

#### Safety

Fireproof classification M1

