



BA7A25040

Slotted panel trunking made of PVC BA7A 25x40mm grey

Technical characteristics

Architecture

Flexible No

Configuration

Side wall configuration Slotted

Electric current

Current leak stable Yes

Dimensions

Trunking height 25 mm

Length 2000 mm

Trunking width 40 mm

Slot width 6 mm

Tongue width 6.5 mm

Cover, door

Lid shape loose

Materials

Colour stone grey

Material group plastic

Type of surface treatment untreated

Installation, mounting

Base punching EN 50085-2-3:1999

Cable

Number of wires 1,5 mm² - 40% filling degree 18

Internal/useful cross section 463 mm²

Number of wires 2,5 mm² - 40% filling degree 13

Number of wires 1,0 mm² - 40% filling degree 24

Standards

European directive RoHS voluntary compliance

UL 94 classification V0

Safety

Fireproof classification M1

