



BA7A40025

Slotted panel trunking made of PVC BA7A 40x25mm grey

Technical characteristics

Architecture

Flexible No

Configuration

Side wall configuration Slotted

Electric current

Current leak stable Yes

Dimensions

Trunking height 40 mm

Length 2000 mm

Trunking width 25 mm

Slot width 6 mm

Tongue width 6.5 mm

Cover, door

Lid shape loose

Materials

Material group plastic

Type of surface treatment untreated

Installation, mounting

Base punching EN 50085-2-3:1999

Fixing type bottom punching

Cable

Number of wires 1,5 mm² - 40% filling degree 22

Internal/useful cross section 605 mm²

Number of wires 2,5 mm² - 40% filling degree 15

Number of wires 1,0 mm² - 40% filling degree 30

Standards

Approvals EN50085-2-3

European directive RoHs voluntary compliance

UL 94 classification V0

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Fireproof classification	M1
temperatur	
Ambient temperature	-5...60 °C