



BRAP0802ELN

Alu-trunking lid 80, anodised

Technical characteristics

Configuration

| | |
|-------------------------|----|
| Antibacterial treatment | No |
| Tamperproof fixing | No |

Compatibility

| | |
|-----------------------|------|
| Product compatibility | BRAP |
|-----------------------|------|

Connectivity

| | |
|-------------------|-----------------|
| Trunking coupling | without coupler |
|-------------------|-----------------|

Dimensions

| | |
|--------|---------|
| Length | 2000 mm |
|--------|---------|

Cover, door

| | |
|------------------|------------|
| Lid mounting | Internal |
| Lid with softlip | No |
| Lid width | 80 mm |
| Cover attachment | Snapped on |

Materials

| | |
|----------------|-----------|
| Material group | aluminium |
|----------------|-----------|

Standards

| | |
|-------------------------|----------------------|
| European directive RoHS | voluntary compliance |
|-------------------------|----------------------|

Safety

| | |
|---------------|-----|
| REACH conform | Yes |
| RoHS conform | Yes |
| Halogen free | Yes |

Use conditions

| | |
|-----------------------|------------|
| Operating temperature | -5...90 °C |
|-----------------------|------------|