



BRAP0802ELN

## Alu-trunking lid 80, anodised

### Technical characteristics

#### Configuration

|                         |    |
|-------------------------|----|
| Antibacterial treatment | No |
| Tamperproof fixing      | No |

#### Compatibility

|                       |      |
|-----------------------|------|
| Product compatibility | BRAP |
|-----------------------|------|

#### Connectivity

|                   |                 |
|-------------------|-----------------|
| Trunking coupling | without coupler |
|-------------------|-----------------|

#### Dimensions

|        |         |
|--------|---------|
| Length | 2000 mm |
|--------|---------|

#### Cover, door

|                  |            |
|------------------|------------|
| Lid mounting     | Internal   |
| Lid with softlip | No         |
| Lid width        | 80 mm      |
| Cover attachment | Snapped on |

#### Materials

|                |           |
|----------------|-----------|
| Colour         | aluminium |
| Material       | Aluminium |
| Material group | aluminium |

#### Standards

|                         |                      |
|-------------------------|----------------------|
| European directive RoHS | voluntary compliance |
|-------------------------|----------------------|

#### Safety

|               |     |
|---------------|-----|
| REACH conform | Yes |
| RoHS conform  | Yes |
| Halogen free  | Yes |

#### Use conditions

|                       |            |
|-----------------------|------------|
| Operating temperature | -5...90 °C |
|-----------------------|------------|