



BRAP651001ELN



## Alu-trunking base 65x100, anodised

### Technical characteristics

#### Configuration

Antibacterial treatment No

#### Compatibility

Device installation compatible format Standard 60mm, CEE, Ecoline, EIB

#### Connectivity

Trunking coupling Junction pins as separate reference

#### Dimensions

Trunking height 65 mm

Length 2000 mm

Trunking width 100 mm

#### Capacity

Maximum number of cables ( $\varnothing$  11 mm, 50% fill) 10 / 28

#### Cover, door

Lid mounting Internal

Lid width 80 mm

Number of lids mountable 1

#### Materials

Material group aluminium

#### Installation, mounting

Base punching Without base punching

#### Cable

Internal/useful cross section 5400 mm<sup>2</sup>

#### Equipment

Number of plugable separators 1

Compartment quantity 1 / 2

#### Standards

European directive RoHS voluntary compliance

#### Safety

REACH conform Yes

RoHS conform Yes

Halogen free	Yes
Impact strength	IK08
<b>Use conditions</b>	
Operating temperature	-5...90 °C