



BRAP651001ELN



## Alu-trunking base 65x100, anodised

### Technical characteristics

#### Configuration

Antibacterial treatment	No
-------------------------	----

#### Compatibility

Device installation compatible format	Standard 60mm, CEE, Ecoline, EIB
---------------------------------------	----------------------------------

#### Connectivity

Trunking coupling	Junction pins as separate reference
-------------------	-------------------------------------

#### Dimensions

Trunking height	65 mm
Length	2000 mm
Trunking width	100 mm

#### Capacity

Maximum number of cables (Ø 11 mm, 50% fill)	10 / 28
--	---------

#### Cover, door

Lid mounting	Internal
Lid width	80 mm
Number of lids mountable	1

#### Materials

Material group	aluminium
----------------	-----------

#### Installation, mounting

Base punching	Without base punching
---------------	-----------------------

#### Cable

Internal/useful cross section	5400 mm <sup>2</sup>
-------------------------------	----------------------

#### Equipment

Number of plugable separators	1
Compartment quantity	1 / 2

#### Standards

European directive RoHS	voluntary compliance
-------------------------	----------------------

#### Safety

REACH conform	Yes
RoHS conform	Yes

Halogen free	Yes
Impact strength	IK08
<b>Use conditions</b>	
Operating temperature	-5...90 °C