



BRP651005HLAN

Flat angle for wall trunking BRP/BRHP/BRAP 65x100mm halogen free alu finish

Technical characteristics

Architecture

Fixing mode Clamping

Configuration

Antibacterial treatment No

Compatibility

Product compatibility BRP / BRAP

Connectivity

Trunking coupling without coupler

Dimensions

Trunking height 65 mm

Length 185 mm

Trunking width 100 mm

Cover, door

Lid with softlip -

Number of lids mountable 0

Materials

Material group plastic

Installation, mounting

Base punching Without base punching

Settings

Angle range 90 °

Accessories included

Accessory configuration Moulded

Standards

European directive RoHs voluntary compliance

Safety

REACH conform Yes

RoHS conform Yes

Impact strength IK07

temperatur

