



BRP651005HLAN



## Flat angle for wall trunking BRP/BRHP/BRAP 65x100mm halogen free alu finish

### Technical characteristics

#### Architecture

Fixing mode	Clamping
-------------	----------

#### Configuration

Antibacterial treatment	No
-------------------------	----

#### Compatibility

Product compatibility	BRP / BRAP
-----------------------	------------

#### Connectivity

Trunking coupling	without coupler
-------------------	-----------------

#### Dimensions

Trunking height	65 mm
Length	185 mm
Trunking width	100 mm

#### Cover, door

Lid with softlip	-
Number of lids mountable	0

#### Materials

Colour	aluminium
Material	PC-ABS
Material group	plastic

#### Installation, mounting

Base punching	Without base punching
---------------	-----------------------

#### Settings

Angle range	90 °
-------------	------

#### Accessories included

Accessory configuration	Moulded
-------------------------	---------

#### Standards

European directive RoHS	voluntary compliance
-------------------------	----------------------

#### Safety

Protection index IP	IP40
REACH conform	Yes
RoHS conform	Yes

**temperatur**

---

Ambient temperature

-30...90 °C