



DR16S

**Din rail board, 1 row 16M, non-transparent door, surface**

**Technical characteristics**

**Architecture**

Intended door position	left
Fixing mode	surface-mounting

**Configuration**

Number of modules	16
-------------------	----

**Compatibility**

Suitable for lightning protection	Yes
-----------------------------------	-----

**Dimensions**

Insertion depth	110 mm
Depth of installed product	115 mm
Internal depth	107 mm
Height of installed product	324 mm
Width of installed product	405 mm
Thickness of sidewall material	1.2 mm

**Cover, door**

Material thickness cover	1.2 mm
Identification of protection index	40
Interlockable	No
Number of keylock of the door	0
Cover type	Closed (plain)
Door leave	single
Transparent cover or door	No

**Materials**

Copper weight of the product	0 kg
Colour	light grey
Material	Steel
Material quality	Steel
Surface appearance	matt
Type of surface treatment	Painted

**Installation, mounting**

Suitable for outdoor use	No
Suitable for ground mounting	No

**Settings**

**Equipment**

Number of rows	1
Number of keys	1
Quantity of rails	1
On/Off switch	No
Number of openings for flange plates	2
Extension possible	Yes

**Safety**

IK protection code against mechanical impacts	IK05
Protection index IP	IP40
Protection class	isol.class I
Glow wire test	according to IEC 61439-1
RoHS conform	Yes
Halogen free	No
Fire resistance	-