



DR64S

Din rail board, 4 row 64M, non-transparent door, surface

Technical characteristics

Architecture

| | |
|------------------------|------------------|
| Intended door position | left |
| Fixing mode | surface-mounting |

Configuration

| | |
|-------------------|----|
| Number of modules | 64 |
|-------------------|----|

Compatibility

| | |
|-----------------------------------|-----|
| Suitable for lightning protection | Yes |
|-----------------------------------|-----|

Dimensions

| | |
|--------------------------------|--------|
| Insertion depth | 110 mm |
| Depth of installed product | 115 mm |
| Internal depth | 107 mm |
| Height of installed product | 774 mm |
| Width of installed product | 405 mm |
| Thickness of sidewall material | 1.2 mm |

Cover, door

| | |
|------------------------------------|----------------|
| Material thickness cover | 1.2 mm |
| Identification od protection index | 40 |
| Interlockable | No |
| Number of keylock of the door | 0 |
| Cover type | Closed (plain) |
| Door leave | single |
| Transparent cover or door | No |

Materials

| | |
|------------------------------|------------|
| Copper weight of the product | 0 kg |
| Colour | light grey |
| Material | Steel |
| Material quality | Steel |
| Surface appearance | matt |
| Type of surface treatment | Painted |

Installation, mounting

| | |
|------------------------------|----|
| Suitable for outdoor use | No |
| Suitable for ground mounting | No |

Settings

Equipment

| | |
|--------------------------------------|-----|
| Number of rows | 4 |
| Number of keys | 1 |
| Quantity of rails | 4 |
| On/Off switch | No |
| Number of openings for flange plates | 2 |
| Extension possible | Yes |

Safety

| | |
|---|--------------------------|
| IK protection code against mechanical impacts | IK05 |
| Protection index IP | IP40 |
| Protection class | isol.class I |
| Glow wire test | according to IEC 61439-1 |
| Fire resistance | - |