



DR80F



5 ROW, 80M DIN RAIL BORAD, FLUSH

Technical characteristics

Configuration

Number of modules	80
-------------------	----

Electric current

Rated current	63 A
---------------	------

Dimensions

Insertion depth	110 mm
Depth of installed product	110 mm
Internal depth	110 mm
Height of installed product	949 mm
Width of installed product	430 mm
Thickness of sidewall material	1.2 mm

Cover, door

Cover type	Door
Transparent cover or door	No

Materials

Type of surface treatment	powder-coated
---------------------------	---------------

Installation, mounting

Suitable for outdoor use	No
--------------------------	----

Settings

Enclosure type	Distributor empty cabinet
----------------	---------------------------

Equipment

Number of rows	5
Number of keys	1
Quantity of rails	5
Extension possible	Yes
Neutral terminal block	Yes

Safety

Protection class	isol.class I
------------------	--------------