



DR96F



**Din rail board, 6 row 96M, non-transparent door, flush**

**Technical characteristics**

**Architecture**

Intended door position left

**Configuration**

Number of modules 96

**Compatibility**

Suitable for lightning protection Yes

**Dimensions**

Insertion depth 110 mm

Depth of wall niche 105 mm

Depth of installed product 5 mm

Internal depth 107 mm

Height of installed product 1109 mm

Width of installed product 430 mm

Width in division units 16

Thickness of sidewall material 1.2 mm

Built-in width 400 mm

**Cover, door**

Material thickness cover 1.2 mm

Identification of protection index 40

Interlockable No

Number of keylock of the door 0

Cover type Closed (plain)

Door leave single

Cover type Cover

Transparent cover or door No

**Materials**

Copper weight of the product 0 kg

Colour light grey

Material quality Steel

Surface appearance matt

**Installation, mounting**

Suitable for outdoor use No

Suitable for ground mounting No

**Settings**

---

Enclosure type	Distributor empty cabinet
----------------	---------------------------

**Equipment**

---

Number of rows	6
Number of keys	1
Quantity of rails	6
On/Off switch	No
Number of openings for flange plates	2
Extension possible	Yes

**Standards**

---

Approvals	BS EN 61439-3
-----------	---------------

**Safety**

---

IK protection code against mechanical impacts	IK05
Protection class	isol.class I
Glow wire test	according to IEC 61439-1
Halogen free	No
Fire resistance	-