



DR96S



Din rail board, 6 row 96M, non-transparent door, surface

Technical characteristics

Architecture

Intended door position	left
------------------------	------

Configuration

Number of modules	96
-------------------	----

Compatibility

Suitable for lightning protection	Yes
-----------------------------------	-----

Dimensions

Insertion depth	110 mm
Depth of installed product	115 mm
Internal depth	107 mm
Height of installed product	1074 mm
Width of installed product	405 mm
Width in division units	16
Thickness of sidewall material	1.2 mm

Cover, door

Material thickness cover	1.2 mm
Identification of protection index	40
Interlockable	No
Number of keylock of the door	0
Cover type	Closed (plain)
Door leave	single
Cover type	Cover
Transparent cover or door	No

Materials

Copper weight of the product	0 kg
Colour	light grey
Material	Steel
Material quality	Steel
Surface appearance	matt

Installation, mounting

Suitable for outdoor use	No
Suitable for ground mounting	No

Settings

Enclosure type

Distributor empty cabinet

Equipment

Number of rows	6
Number of keys	1
Quantity of rails	6
On/Off switch	No
Number of openings for flange plates	2
Extension possible	Yes

Safety

IK protection code against mechanical impacts	IK05
Glow wire test	according to IEC 61439-1
Halogen free	No
Fire resistance	-