



EE812

μ IP41

Presence detector 360°, 1/10V, flush mounted, white

Technical characteristics

Architecture

Bus system Without

Main electrical features

Rated operational voltage Ue 230 V

Frequency 50 Hz

Dimensions

Height of installed product 31 mm

Width of installed product 100 mm

Reach distance

Max. transmission range 12m

Power supply

Supply voltage 230 V

Detection

Detection angle 360 °

Frontal detecting distance 7 m

Side detecting distance 13 m

Materials

Colour pure white

RAL colour RAL 9010 - Pure white

Material plastic

Lighting control

Brightness measurement range 5 / 1200 Lux

Installation, mounting

Maximum Mounting Height 4 m

Settings

Response value sensitivity adjustable Yes

Equipment

Angle of horizontal detection 360 °

Use conditions

Operating temperature 0...45 °C

Storage/transport temperature -10...60 °C