



EPN050



Auxiliary contact for centralised control

Technical characteristics

Configuration

Number of modules	0.5
-------------------	-----

Main electrical features

Rated operational voltage Ue	110 / 230 V
Frequency	50 Hz

Voltage

Command voltage AC	110 / 230 V
--------------------	-------------

Electric current

Rated current	1 A
---------------	-----

Dimensions

Depth of installed product	58 mm
Height of installed product	85 mm
Width of installed product	8.9 mm

Power

Total power loss under IN	0.1 W
---------------------------	-------

Connection

Connection cross-sect. flexible conductor	1 / 6mm ²
Connection cross-sect. rigid cable	1,5 / 10mm ²
Type of connection	with screw

Safety

REACH conform	No
RoHS conform	Yes
Halogen free	No

Use conditions

Operating temperature	-5...40 °C
Storage/transport temperature	-40...80 °C