



EPN051



Auxiliary contact 1NC+1NO

Technical characteristics

Configuration

Number of modules	0.5
-------------------	-----

Main electrical features

Rated operational voltage U_e	250 V
---------------------------------	-------

Voltage

Rated insulation voltage	250 V
--------------------------	-------

Electric current

Rated current	2 A
---------------	-----

Dimensions

Depth of installed product	58 mm
----------------------------	-------

Height of installed product	83 mm
-----------------------------	-------

Width of installed product	8.75 mm
----------------------------	---------

Power

Total power loss under IN	0.1 W
---------------------------	-------

Installation, mounting

Factory fitted	No
----------------	----

Connection

Connection cross-sect. flexible conductor	1 / 6mm ²
---	----------------------

Connection cross-sect. rigid cable	1,5 / 10mm ²
------------------------------------	-------------------------

Number of contacts	2
--------------------	---

Type of contacts	1NC+1NO
------------------	---------

Type of connection	with screw
--------------------	------------

Safety

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Halogen free	No
--------------	----

Use conditions

Operating temperature	-5...40 °C
-----------------------	------------

Storage/transport temperature	-40...80 °C
-------------------------------	-------------