



EU300

control relay triphased phase 400V

Technical characteristics

Configuration

Number of modules 2

Main electrical features

Frequency 50/60 Hz

Electric current

Acceptable current rating with AC1 8 A

Dimensions

Depth of installed product 64 mm

Height of installed product 85 mm

Length 64 mm

Width of installed product 35 mm

Power

Total power loss under IN 4 W

Installation, mounting

Mounting type din-Rail

Connection

Type of contacts 1 changeover

Safety

Protection index IP IP20

Use conditions

Operating temperature -20...55 °C

Storage/transport temperature -40...70 °C